



NON-FUSIBLE MECHANICAL INTERLOCK

PS5100MIR7W | [Pass & Seymour](#)

FEATURES & BENEFITS

Four pole, Five wire, Non-Fusible Mechanical Interlock Receptacle. 100 amp, 3ØY, 277/480 vac.



- Top or Bottom feed.
- Unit shipped with no holes drilled; a top and bottom feed spot drill is provided for locating hole saw or knockout.
- End user decides at installation whether top or bottom feed is appropriate.
- No closure plug kits required.

SPECIFICATIONS

GENERAL INFO

Type: Pin & Sleeve Non-Fusible Mechanical Interlock Receptacle
Number Of Poles: 4
Number Of Wires: 5

LISTING AGENCIES/THIRD PARTY CERTIFICATIONS

RoHS: Yes
UL Listing No: E31169
UL Standard: Yes
UN SPSC: 39121403

TECHNICAL INFORMATION

Amps: 100A
Volts: 3ØY 277/480VAC
Volts (AC): 277/480

BUY AMERICAN ACT COMPLIANCE

Country Of Origin: UNITED STATES OF AMERICA
Buy American Act Status: Buy American Act Compliant

