



Pass and Seymour
20A Single Pole, Double Throw White
Part No. 1251W

Single-Pole, Double-Throw Manual Control Switch, 20A, 120/277V.



Features & Benefits

Oversize silver alloy contacts for long life and better heat dissipation.

Side wired terminals accept #14 - #10 AWG copper or copper-clad conductors.

Fiber terminal insulation barriers standard.

Can be mounted in standard device boxes or in NEMA 1 sheet steel enclosures.

Bodies, covers, and toggles molded of durable nylon.

Single Pole-Double Throw and Double Pole-Double Throw.

Locking Switches supplied with one 1498-NT key.

Normally open.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------------|------------------------|---------------------|-------------------------|
| Product Line | Pass & Seymour | Color | White |
| Finish | Matte | UPC Number | 785007125160 |
| Country Of Origin | Mexico | Features | Durable |
| Switch Type | Toggle | Number of Switches | 1 |
| Application Sector | Commercial, Industrial | Wall Plate Included | No |
| Standard | UL listed | Warranty Type | 1-Year Limited Warranty |
| Type | Manual Controller | | |

Dimensions

| | | | |
|-------------------|----------|------------------|----------|
| Product Width US | 1.5 in | Product Depth US | 1.469 in |
| Product Height US | 3.281 in | | |

Listing Agencies / 3rd Party Agencies

| | | | |
|------------|-----|--------------|-----|
| CSA Listed | Yes | cULus Listed | Yes |
|------------|-----|--------------|-----|

Technical Information

| | | | |
|------------------------|--|-----------------------|-----------|
| Load Rating | 20 A @ 120/277 VAC | Connection Location | Side Only |
| Terminal Accommodation | #14 AWG - #10 AWG | Number of Gangs | 1 |
| Throw Type | Double Throw | Amperage | 20 A |
| Number of Poles | Single Pole | Requires Neutral Wire | Yes |
| Indoor/Outdoor | Indoor | Mounting Type | Wall Box |
| Wire Connection Type | Screw Terminals | Voltage | 120/277 V |
| Load Type | CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon | | |