



## WEATHER-RESISTANT COMMERCIAL GRADE RECEPTACLES, WHITE

WR20TRW | [Pass & Seymour](#)

### FEATURES & BENEFITS

Weather-Resistant Commercial Grade Receptacles, 20 amp, 125 volts, White, WR20TRW



- Auto-ground clip assures positive ground.
- WR marking on face as required by UL Standard.
- Zinc-plated steel mounting screws for greater ease of installation and removal in wet or damp locations.
- Strap tabs wrap around face to prevent strap from separating from face and back body.
- Tri-drive brass terminal screws. Internal screwpressure plate back and side wire capability. Two back wire holes for more wiring flexibility.
- Heavy-duty, brass strap for added strength and ground conductivity.
- UV-resistant nylon face for longer life under adverse environmental conditions.
- Two drive screws anchor strap to backbody and face where abrupt removal torque is strongest.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- .032 inch thick brass triple-wipe power contacts for lasting retention.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

### SPECIFICATIONS

#### GENERAL INFO

Color: White  
Type: Receptacles  
Features: Weather-Resistant  
Number Of Poles: 2  
Number Of Wires: 3  
Special Features: Weather-Resistant, Tamper-Resistant  
Style: Duplex

## **LISTING AGENCIES/THIRD PARTY CERTIFICATIONS**

RoHS: Yes  
CSA Listing Info: C22.2 No. 42  
CSA Standard: Yes  
UL Listing No: UL498  
UL Standard: Yes  
UN SPSC: 39121406

## **DIMENSIONS**

Depth (US): 1.130"  
Height (US): 3.281"  
Width (US): 1.322"

## **TECHNICAL INFORMATION**

Amps: 20A  
NEMA Configuration Number: 5-20R  
Volts: 125V  
Volts (AC): 125  
Capacity: Duplex  
Grade Type: Commercial

## **BUY AMERICAN ACT COMPLIANCE**

Country Of Origin: CHINA  
Buy American Act Status: Trade Agreement Act Compliant