



radiant Collection  
**radiant® Tamper-Resistant Weather-Resistant 15A Duplex Self-Test GFCI Receptacles with SafeLock® Protection, Light Almond**  
Part No. 1597TRWRLA



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. Also including tamper and weather resistance, this model was designed for use on decks, patios, pool areas, and other outdoor spaces. Maximize safety, in style, with GFCI protection featuring the sleek, clean lines of radiant. GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Designed with weather-resistance for use in outdoor locations such as decks, patios and pool areas. \*Must be installed in weatherproof enclosure per NEC requirements.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

Replaces any standard receptacle with ease, in as little as 10 minutes.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

|                       |  |                    |  |
|-----------------------|--|--------------------|--|
| Product Line          | Pass & Seymour   | Color              | Light Almond                                 |
| UPC Number            | 785007036497   | Country Of Origin  | China  |
| Number of Receptacles | 2  | Features           | Self-Test, Weatherproof                      |
| Outlet Type           | GFCI, Tamper-Resistant, Weather-Resistant, Weather-Resistant | Application Sector | Commercial, Multi-Dwelling Unit, Residential |
| Wall Plate Included   | Yes  | Standard           | cULus, UL Listed, FSUL                       |
| Warranty Type         | 1-Year Limited Warranty                                      | Type               | Outlet                                       |

### Dimensions

|                   |         |                  |         |
|-------------------|---------|------------------|---------|
| Product Width US  | 1.73 in | Product Depth US | 1.13 in |
| Product Height US | 4.2 in  |                  |         |

### Listing Agencies / 3rd Party Agencies

|              |     |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Additional Information

|                               |     |
|-------------------------------|-----|
| Product Environmental Profile | Yes |
|-------------------------------|-----|

Technical Information

|                     |         |                          |   |
|---------------------|---------|--------------------------|---|
| Is Tamper-Resistant | Yes     | Connection Location      | Back and Side                             |
| Frequency Rating    | 60 Hz   | Connection               | Back and side wire                        |
| Number of Wires     | 3       | Number of Gangs          | 1   |
| Amperage            | 15 A    | Number of Poles          | Double Pole                               |
| Indoor/Outdoor      | Both    | NEMA Configuration Code  | 5-15R                                     |
| Mounting Type       | Box     | Wire Connection Type     | Internal Pressure Plates, Screw Terminals |
| Voltage             | 125.0 V | Environmental Conditions | 95% Humidity, UL 94 V2                    |