



Ideal for replacing outlets by kitchen or bathroom sinks, this combination device from the radiant® Collection includes a tamper-resistant GFCI outlet paired with a sealed, built-in LED light which automatically turns on in the dark for easier nighttime navigation. Designed for safety, this self-testing GFCI outlet complies with National Electrical Code and makes trips easier to recognize and fix than GFCI breaker alternatives, thanks to accessible indicator light and reset button right on the outlet. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Hidden sensor controls night light based on ambient light, automatically turning on when it is dark.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with 'invisi-shutters' for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style.

Specifications

General Info

Color	Light Almond	UPC Number	785007048407
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential/Commercial	Number of Receptacles	2
Warranty Type	1-Year Limited Warranty	Standard	cULus, UL Listed, FSUL

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Number of Gangs	1	Voltage	125 V
Mounting Type	Box	Trip Range	4 to 6 mA
Connection	Back and Side Wire	Frequency Rating	60 Hz
Interrupt Rating	4 A	Environmental Conditions	95% Humidity, UL 94 V2
