



Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the indicator light flashes to signal that the GFCI should be replaced. It also has our proven SafeLock™ Protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected. For detailed Tamper-Resistant receptacle information, visit our [Tamper-Resistant Receptacles page](#).

Features & Benefits

Alarm rated at 60 db at 10 feet

One-piece, brass, triple-wipe power contacts for lasting retention

Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected

Feed-thru wiring configuration allows GFCI to protect downstream receptacles

Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly

Mounting screws are shipped captive in the device and wall plate for easier installation

Dual-direction test and reset button colors match the device face

Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007048001	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm
Outlet Type	Commercial, Indoor, GFCI, Tamper-Resistant, Self-Test	Application Sector	Residential/Commercial
Standard	cULus, UL Listed, FSUL	Type	Outlet

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

Product Environmental Profile Yes

Technical Information

Is Tamper-Resistant	Yes	Interrupt Rating	4 A
Frequency Rating	60 Hz	Trip Range	4 to 6 mA
Connection	Back and Side Wire	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
Voltage	125 VAC	Environmental Conditions	95% Humidity, UL 94 V2
