


Legrand keyed LC fiber solutions provide a simple and convenient way to physically prevent the user from making an unauthorized connection by blocking access to specific optical ports, whether they are at a workstation outlet or in a telecommunications room or data center. This is particularly important for government, finance, military and other facilities where multiple networks having different security level access requirements may be co-located.



Features & Benefits

- A factory-cleaved 900um fiber stub ensures ease of use and optimal performance
- The solution to managing multiple networks with reduced risks
- LC SECURE products feature twelve color-coded, keyed designs to limit improper connections networks.
- Internal keying feature prevents tampering
- 50/125 µm and 9/125 µm laser-optimized fiber types available
- 1.6 in boot protects the splice for easy cable management
- LC Keyed cadapters prevent improper connection of separate networks with common access points
- Each LC secure adapter will mate only with same-color LC secure connector
- High quality 1.25 mm zirconia ferrules used

Specifications

General Info

Type Connector

Technical Information

Fiber Size	9/125	Temperature Rating	-40 to +75°C
Service Life	< 0.2dB typical change,500 matings		