



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances and in commercial settings, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

### Features & Benefits

Alarm rated at 60 db at 10 feet	One-piece, brass, triple-wipe power contacts for lasting retention
Conducts an automatic test every three seconds, ensuring it's always ready to protect. If the device fails the test, the trip indicator light (red LED) flashes to signal that the GFCI should be replaced	Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the receptacle is disconnected
Feed-thru wiring configuration allows GFCI to protect downstream receptacles	Prevents line-load reversal miswire: no power to the face or downstream receptacles if wired incorrectly
Mounting screws are shipped captive in the device and wall plate for easier installation	Dual-direction test and reset button colors match the device face
Thinner than competitors' GFCI Receptacles: leaves more room for wires in the box	

### Specifications

#### General Info

Product Line	Pass & Seymour	Color	Light Almond
UPC Number	785007048001	Country Of Origin	China
Number of Receptacles	2	Features	Audible Alarm, Self-Test
Outlet Type	GFCI, Self-Test, Tamper-Resistant	Application Sector	Commercial, Multi-Dwelling Unit, Residential
Wall Plate Included	Yes	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty		

#### Dimensions

Product Width US	1.73 in	Product Depth US	1.03 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Is Tamper-Resistant	Yes	Connection Location	Back and Side
Number of Wires	3	Amperage	20 A
Number of Poles	Double Pole	Indoor/Outdoor	Indoor
NEMA Configuration Code	5-20R	Wire Connection Type	Internal Pressure Plates, Screw Terminals
Voltage	125.0 V	Environmental Conditions	95% Humidity, UL 94 V2