



GFCI receptacles from the radiant® Collection self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. Meeting National Electrical Code requirements for ground fault protection in the home, GFCI receptacles make it easier to recognize and fix trips right where they happen – no more confusion at the breaker box. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately. Spec-Grade devices are engineered to meet federal specifications for use in commercial installations.

Features & Benefits

- Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI receptacles make it easier to fix trips with a reset button right on the device.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.
- Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Extends GFCI protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

NAFTA-Compliant devices are ideal for use on projects subject to the provisions of the Buy America Act.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	Mexico
Number of Receptacles	2	Outlet Type	GFCI, Indoor, Residential, Self-Test, Tamper-Resistant
Application Sector	Residential/Commercial	Standard	cULus, UL Listed, FSUL
Warranty Type	1-Year Limited Warranty	Type	Outlet

Dimensions

Product Width US	1.73 in	Product Depth US	1.25 in
Product Height US	4.2 in		
Listing Agencies / 3rd Party Agencies			
cULus Listed	Yes		
Additional Information			
Product Environmental Profile	Yes		
Technical Information			
Interrupt Rating	4 A	Frequency Rating	60 Hz
Trip Range	5±1 mA	Number of Gangs	1
Amperage	20 A	Number of Poles	Double Pole
Indoor/Outdoor	Indoor	NEMA Configuration Code	5-20R
Mounting Type	Box	Voltage	125.0 V
Environmental Conditions	95% Humidity, UL 94 V2		