



Wiremold  
24S7218IGX99IV Steel Plugmold® Multioutlet Strip  
Part No. 24S7218IGX99IV



6' Steel Plugmold Multioutlet Strip with 4 duplex receptacles spaced at 18", IG

## Features & Benefits

Steel Raceway. Provides superior strength for any dry location installation with greater wire capacity than V2000.

Ivory ScuffCoat finish. Durable scratch resistant finish.

Removable cover. Allows easy access to wiring for changes or additions.

Full range of fittings. Provides a complete wiring solution.

Single-and-dual-gang boxes. Wire devices into the raceway system or protect a Plugmold® strip with a surge or GFCI device.

Factory wired Plugmold® sections available in 3', 5', and 6' lengths with 20A, 120V receptacles. Ideal for short runs requiring additional outlets in electrically busy areas.

Single or alternating circuit. Meets virtually any circuit requirement.

Choice of receptacle spacing. Center spacing between receptacles of 6", 12" and 18".

Simplex receptacle. More spacing options available.

Duplex receptacle. Aesthetically pleasing, functional 20A duplex for the 24S (2400) Series.

Customization available. All products can be modified to accommodate virtually any application.

## Specifications

### General Info

UPC Number	786776165197	Country Of Origin	United States
Product Line	Wiremold	Application Sector	Commercial
Type	Plugmold	Number of Receptacles	4

---

Standard

cULus Listed Base & Blank Cover: File E4376  
Guide RJBT. Multioutlet Assemblies: File E15191  
Guide PVGT. Fittings: File E41751 Guide RJPR.  
Base & Blank Cover & Plugmold Series w/Snapcoil  
Harness: Meets Article 386 of NEC. Meets Section  
12-3032 of CEC. Plugmold Wired Sections: Meets  
Article 380 of NEC. Meets Section 12-3032 of CEC.

---

### Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes	cULus ListingNumber	E15191
--------------	-----	---------------------	--------

---

### Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

### Additional Information

---

RoHS Conformant	Yes
-----------------	-----

---

### Technical Information

---

Voltage	125 V	Enclosure Type	Steel
---------	-------	----------------	-------

---

Environmental Conditions	Dry interior locations
--------------------------	------------------------

---