




Pass and Seymour  
Discontinued - Illuminated Decorator Switch, Brown  
Part No. 2625



Single Pole, Back and Side Wire, Illuminated Decorator Switch, 20 amps, 120 volts, Brown. 

## Features & Benefits

Impact-resistant polycarb back body and frame.

Unique single rocking butterfly contact provides long term consistent performance with significantly fewer moving parts.

Terminals made of high conductivity brass and serrated for maximum wire gripping.

Integral auto-ground clip for positive ground to metal boxes.

All terminal screws backed out, ready-to-install.

Cushioned thermoplastic paddle assures smooth, quiet, long term operation.

Internal screw-pressure-plate back and side wire capability for easy installation with #14 - #10 stranded or solid copper/copper clad wire.

Silver alloy contacts integrally formed to the butterfly actuator assures reliable performance.

Tri-drive ground, terminal, and mounting screws.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Brown
Finish	Matte	UPC Number	785007243079
Country Of Origin	Mexico	Features	Decorator Style, Illuminated
Switch Type	Paddle	Number of Switches	1
Application Sector	Commercial, Residential	Wall Plate Included	No
Standard	UL 20	Warranty Type	1-Year Limited Warranty

Type	Decorator, Switch		
Listing Agencies / 3rd Party Agencies			
CSA Listed	Yes	cULus Listed	Yes
Technical Information			
Operating Temperature Min	-4 °F	Load Rating	20 A @ 120 VAC
Connection Location	Back and Side	Horsepower Rating	1 HP @ 120 VAC, 2 HP @ 240 VAC
Terminal Accommodation	#14 AWG - #10 AWG	Operating Temperature Max	140 °F
Number of Gangs	1	Throw Type	Single Throw
Amperage	20 A	Number of Poles	Single Pole
Requires Neutral Wire	No	Indoor/Outdoor	Indoor
Mounting Type	Wall Box	Operating Temperature	-20°-60°C, -4°-140°F
Wire Connection Type	Screw Terminals	Voltage	120 VAC
Load Type	CFL, Fluorescent, Halogen, Incandescent, LED, Universal, Xenon		