



Heavy-Duty Decorator Hospital Grade Duplex Receptacle Back and Side-Wire 15A 125V



## Features & Benefits

- Corrosion-resistant, plated steel strap locked into assembly to prohibit strap from bending away from body. One-piece, brass, triple-wipe power contacts for lasting retention.
- Heavy-duty compact design for easier installation and long lasting performance. Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Impact-resistant nylon face. Terminal compartments isolated from each other for positive conductor containment.
- Side and internal screw-pressure-plate back wire accepts #14 - #10 AWG solid or stranded wire. All devices fit standard #26 opening wall plate.
- Tri-drive terminal and mounting screws. Auto-ground clip assures positive ground.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents). For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007784817	Country Of Origin	Mexico
Application Sector	Commercial	Standard	UL498, cUL CSA

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

---

## Technical Information

---

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
Number of Poles	Double Pole	Wire Size	#14 - #10
Voltage	125 V	Environmental Conditions	Flammability: UL94 V2

---