



"SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure"

## Features & Benefits

UL and CSA Listed

Patent Pending

Anti-microbial Additive Resistant to Scuffing and Cleaning

Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria by > 99.97%

RoHS Compliant (Non-Halogenated)

Resistant to High Pressure Hose-down applications

Keyed Body and Cover for Alignment

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.

NSF (National Sanitation Foundation) Certified

Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi

Escherichia [E.Coli]: - Log reduction > 4.8, reduced surface bacteria by > 99.99%

Salmonella : Log Reduction > 3.6, reduces surface bacteria by > 99.97%

Independently tested and Certified to JIS Z2801 standards

Tongue & Groove Environmental Sealing

NEMA Type 4, 4x, 6, 6P and IP67 Protection

## Specifications

### General Info

Color Yellow

UPC Number 785007057089

Country Of Origin United States

Product Line Pass & Seymour

Standard UL Listed, CSA Listed

### Technical Information

Number of Poles Double Pole

Voltage 125 V

Phase Single

---

**Wire Size** 14 AWG min - 10 AWG max

---

**Number of Wires** 3

---

**Environmental Conditions** Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized

---