



Pass and Seymour  
SteriGuard™ Antimicrobial Turnlock Connector 20A, 3Φ250V  
Part No. 27W75AM



"SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of Escherichia coli, Gram (-) and Staphylococcus aureus, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure"

## Features & Benefits

UL and CSA Listed

NSF (National Sanitation Foundation)  
Certified

Patent Pending

Anti-microbial Additives Embedded in  
polymer and inhibits Growth of Bacteria,  
Molds, Mildews and Fungi

Anti-microbial Additive Resistant to Scuffing and Cleaning

Escherichia (E.Coli): - Log reduction > 4.8,  
reduced surface bacteria by > 99.99%

Staphylococcus (Staph), MRSA: - Log Reduction > 4.3, reduces surface bacteria  
by > 99.97%

Salmonella : Log Reduction > 3.6, reduces  
surface bacteria by > 99.97%

RoHS Compliant (Non-Halogenated)

Independently tested and Certified to JIS  
Z2801 standards

Resistant to High Pressure Hose-down applications

Tongue & Groove Environmental Sealing

Keyed Body and Cover for Alignment

NEMA Type 4, 4x, 6, 6P and IP67 Protection

SteriGuard: Anti-microbial Wiring Devices are ideal for a wide range of  
applications including food and beverage preparation, procession, & packaging:  
agriculture, pharmaceutical, and health care.

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007057287	Country Of Origin	United States
Standard	UL Listed, CSA Listed		

---

## Technical Information

---

Phase	Three	Number of Wires	4
Number of Poles	3-Way	Wire Size	14 AWG min - 10 AWG max
Voltage	250 V	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed materials are UV stabilized

---