



Pass and Seymour  
**Turnlok® SteriGuard™ Antimicrobial Connector 15A, 250V, Yellow**  
Part No. 25W49AM



SteriGuard Anti-Microbial Wiring Devices provide excellent protection against the growth of microbes on all surfaces. Independent testing proves the ability of these devices to inhibit the growth of *Escherichia coli*, Gram (-) and *Staphylococcus aureus*, Gram (+) providing long lasting benefits to manufacturers beyond conventional cleaning methods. Rated watertight for 1,500 psi high-pressure

## Features & Benefits

UL and CSA Listed	NSF (National Sanitation Foundation) Certified
Patent Pending	Anti-microbial Additives Embedded in polymer and inhibits Growth of Bacteria, Molds, Mildews and Fungi
Anti-microbial Additive Resistant to Scuffing and Cleaning	<i>Escherichia</i> (E.Coli): - Log reduction greater than 4.8, reduced surface bacteria by greater than 99.99%
<i>Staphylococcus</i> (Staph), MRSA: - Log Reduction greater than 4.3, reduces surface bacteria by greater than 99.97%	<i>Salmonella</i> : Log Reduction Greater Than 3.6, reduces surface bacteria by Greater Than 99.97%
RoHS Compliant (Non-Halogenated)	Independently tested and Certified to JIS Z2801 standards
Resistant to High Pressure Hose-down applications	Tongue & Groove Environmental Sealing
Keyed Body and Cover for Alignment	NEMA Type 4, 4x, 6, 6P and IP67 Protection
Steriguard: Anti-microbial Wiring Devices are ideal for a wide range of applications including food and beverage preparation, procession, & packaging: agriculture, pharmaceutical, and health care.	

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Yellow
UPC Number	785007057126	Country Of Origin	United States

Standard	UL Listed, CSA Listed		
Dimensions			
Product Width US	1.85 in	Product Depth US	4.03 in
Product Height US	1.85 in		
Technical Information			
Phase	Single	Number of Wires	3
Amperage	15 A	Number of Poles	Double Pole
Wire Size	18 - 12 AWG	Environmental Conditions	Moisture Resistance NEMA 4, 4X, 12, 6, 6P/IP65, 66, 67 (Plug & Connector only) Flammability UL94V0 (boxes & wiring device interiors) Operating Temperature -40°C (without impact) to +60°C continuous UV resistance All exposed material s are UV stabilized