

TVSS Specification Grade Quad Receptacle, 20A 125V



Features & Benefits

Rugged nylon face and body withstands impacts and hard use.

Built-in wire stripping gauge.

Outward-facing ground terminals make handling up to four straight or angled plugs easy and convenient.

Heavy-duty, phosphor bronze contacts.

Shielding walls guard against live-circuit-to-ground shorts.

Split circuit break-off tabs.

UL and CSA listed.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

| | | | |
|--------------------|-------------------------|-------------------|---|
| Product Line | Pass & Seymour | Color | Blue |
| UPC Number | 785007496307 | Country Of Origin | Mexico |
| Application Sector | Commercial, Residential | Standard | UL1449, UL498: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse). |

Technical Information

| | | | |
|-----------------|------|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 65° C |
| Amperage | 20 A | Number of Poles | Double Pole |

Wire Size

14 - 12 AWG

Environmental Conditions

Flammability: UL94 V2 and
UL94-5 VA
