


Routing power, data, and A/V – neatly and simply – from up there to down here; that’s what Tele-Power® Poles are all about. Their sole purpose is to get the business end of your wire and cabling needs down to your workstation, equipment, or modular furniture. Specifically, in away-from-the-wall locations in open commercial office areas, schools, labs, stores and other sites. Whatever power, data, or A/V wiring you need to bring down to the desk, workstation, or cash registers, Wiremold Tele-Power Poles handle all of your needs effortlessly. For modular office furniture – our poles easily provide the hook up to feed office partitions. The poles are also available with specialized electrical circuits such as dedicated/isolated ground. Vertical drop poles give you the flexibility and capacity to devote both sides of the pole for single or dual service feeds. Legrand/Wiremold offers the broadest selection of open space solutions. With standard, custom and configurable products, you can rest assured that the right solution is readily available and adaptable to your current and future work environments.



Features & Benefits

For 30TP-2V / 30TC-2V and 30TP-4V / 30TC-4V Series. 12" (305mm) long. Communication covers for additional voice/data connectors. Each cover includes Kos for four RJ11/RJ45 connectors (.760" x .576" (19.3mm x 14.6mm)), mouse hole for exiting communication cables (grommet furnished).

Specifications

General Info

Product Line	Wiremold	Color	Ivory
UPC Number	786776101256	Country Of Origin	United States
Application Sector	Commercial	Standard	cULus Listed Multioutlet Assemblies: File E15191, E178348 Guide PVGT. Raceway Fittings: File E41751 Guide RJPR. Accessories: File E53857 Guide RVUR Meets Article 380 & 386 of NEC.

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E53857	cULus Listed	Yes
---------------------	--------	--------------	-----

Buy American Act Compliance

NAFTA	Yes
-------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----
