




Wiremold  
CableSmart 40N2 Twin Cover Device Bracket Fitting  
Part No. 40N2F31V



Used for power or communications devices in a single compartment. Accepts 5507 Series Faceplates. For use with Ortronics TracJack Individual Jack System, Ortronics Series II Front-Loading Module System, and Wiremold Open System Communications Modules. NOTE: CM-EPLA End Plates are required when using Wiremold communication modules and Pass and Seymour inserts. S2-EPL End Plates are required when using Ortronics Series II inserts. To mount TracJack inserts, use 5507-4TJ or 5507-6TJ Faceplates.

## Features & Benefits

Used for power or communications devices in a single compartment. Accepts 5507 Series Faceplates. For use with Ortronics TracJack Individual Jack System, Ortronics Series II Front-Loading Module System, and Wiremold Open System Communications Modules. NOTE: CM-EPLA End Plates are required when using Wiremold communication modules and Pass and Seymour inserts. S2-EPL End Plates are required when using Ortronics Series II inserts. To mount TracJack inserts, use 5507-4TJ or 5507-6TJ Faceplates.

## Specifications

### General Info

Product Line	Wiremold	UPC Number	786776136661
Country Of Origin	United States	Application Sector	Residential/Commercial
Standard	cULus Listed Raceway: File E90378 Guide RJTX. Complies with Flammability requirements of UL-5A. Fittings: File E90377 Guide RJYT. Meets Article 388 of NEC. UL Listed for up to 600V. Meets Section 12-1600 of CEC.	Type	Raceway

### Dimensions

Product Height US	2.187 in	Product Length US	5.25 in
-------------------	----------	-------------------	---------

### Listing Agencies / 3rd Party Agencies

cULus ListingNumber	E90377	cULus Listed	Yes
---------------------	--------	--------------	-----

---

Buy American Act Compliance

---

NAFTA	Yes
-------	-----

---

Additional Information

---

RoHS Conformant	Yes	Product Environmental Profile	Yes
-----------------	-----	-------------------------------	-----

---

Technical Information

---

Voltage	600.0 V
---------	---------

---