



Quiktron
Q-Series Patch Cords, CAT5E, Non-Booted, Blue, 14 FT
Part No. 560-110-014



Q-Series patch cords are a perfect solution for when cost and speed of delivery are top priority. Designed to perform to TIA-568.2-D standards, Q-Series cords are available in a full range of colors and lengths, stocked and ready to order.

Features & Benefits

Connector: 50micron gold plated RJ45 male to male

Conductor: 24AWG stranded copper

Warranty Type: Lifetime warranty

Price Sensitive: Perfect solution for when cost and speed of delivery are top priority

Standards Compliant: Perform to TIA-568.2-D standards

Specifications

General Info

| | | | |
|--------------|-------------------|--------------------|------------------------|
| Product Line | Quiktron | Color | Blue |
| UPC Number | 884815750349 | Country Of Origin | Vietnam |
| Features | Standard Diameter | Application Sector | Commercial, Industrial |
| Type | Copper Patch Cord | | |

Dimensions

| | | | |
|-------------------|---------|-------------------|---------|
| Product Weight US | 0.35 lb | Product Length US | 14.0 FT |
| Cable Length | 14 ft | | |

Additional Information

| | |
|----------------|-----|
| RoHS Compliant | Yes |
|----------------|-----|

Technical Information

| | | | |
|-----------------------------|---------------------------|---------------------------|----------------|
| Jacket Material | PVC | Operating Temperature Min | -10 °C |
| Category Performance Rating | Cat5e | Wire Gauge | 24 AWG |
| Storage Humidity | 0-90% RH (Non-Condensing) | Plating Specification | 50 μ in Gold |
| Jacket Application | Riser Rated | Bend Radius | 0.82 in |
| Shielded/Unshielded | Unshielded | Termination Style | Pre-Terminated |
| Conductor Stranding | Stranded | Operating Temperature Max | 60 °C |
| Jacket Rating | CM Rated | Cable Diameter | 0.205 in |
| Braid | Non-braided Wiring | Operating Temperature | -10°-60°C |
| Operating Humidity | 0-90% RH (Non-Condensing) | Conductor Material | Copper |
| Voltage | 300.0 V | Storage Temperature | -40° - 60° C |