



Pass and Seymour
Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 15A, 250V, Ivory
Part No. 56621



Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 15amp 250volt Ivory

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around face to prevent strap from separating from face and back body.

High strength nylon face.

Eight back wire holes.

For covering patents, see www.legrand.us/patents.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

| | | | |
|--------------------|------------|--------------|-------------------------------|
| Color | Ivory | UPC Number | 785007566215 |
| Country Of Origin | Mexico | Product Line | Pass & Seymour |
| Application Sector | Commercial | Standard | cULus UL498, CSA C22.2 No. 42 |

Listing Agencies / 3rd Party Agencies

| | | | |
|--------------|-----|---------------------|--------|
| cULus Listed | Yes | cULus ListingNumber | 140596 |
|--------------|-----|---------------------|--------|

Technical Information

| | | | |
|--------------------|--|--------------------------|--------------------------------|
| Number of Poles | Double Pole | Voltage | 250 V |
| Connection | Back and side wire | Dielectric Strength | Withstands 2000V minimum |
| Temperature Rating | Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact | Wire Size | #14 - #10 |
| Number of Wires | 3 | Environmental Conditions | Flammability: UL94 V2 |
