



Pass and Seymour  
20A 125V Industrial Extra Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, White  
Part No. 5362AW



Industrial Extra Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 125V

## Features & Benefits

One-piece brass mounting strap with integral ground.

Two drive screws anchor strap to back body and face.

.036 inch thick, brass, triple-wipe power contacts for lasting retention.

Oversized #10 deep tri-drive head brass terminal and ground screws.

External screw-pressure-plate back wire clamps with #10 brass terminal screws for visual assurance of a good connection.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Exclusive patented feature, circuit label on face allows permanent circuit identification.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Exclusive patented feature, external screw-pressure-plate back wire clamp on ground terminal for faster, easier installation.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

## Specifications

### General Info

|                   |                |                       |              |
|-------------------|----------------|-----------------------|--------------|
| Product Line      | Pass & Seymour | Color                 | White        |
| Finish            | Matte          | UPC Number            | 785007528190 |
| Country Of Origin | Mexico         | Number of Receptacles | 2            |

|  |                          |                    |  |
|--|--------------------------|--------------------|--|
| Application Sector                           | Commercial, Industrial   | Standard           | cULus UL498, CSA C22.2 No. 42, FEDSPEC |
| Type   | Outlet                   |                    |  |
| <b>Dimensions</b>                            |                          |                    |  |
| Product Width US                             | 1.625 in                 | Product Depth US   | 0.9 in                                 |
| Product Height US                            | 2.75 in                  |                    |  |
| <b>Listing Agencies / 3rd Party Agencies</b> |                          |                    |  |
| cULus ListingNumber                          | 140596                   | cULus Listed       | Yes                                    |
| <b>Technical Information</b>                 |                          |                    |  |
| Dielectric Strength                          | Withstands 2000V minimum | Temperature Rating | -40° - 60° C                           |
| Amperage                                     | 20 A                     | Number of Poles    | Double Pole                            |
| Wire Size                                    | 14 - 10 AWG              | Indoor/Outdoor     | Indoor                                 |