



Pass and Seymour  
20A 250V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, White  
Part No. 5862W

Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 250V



## Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.	Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
Strap tabs wrap around face to prevent strap from separating from face and back body.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
High strength nylon face.	Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
Auto-ground clip assures positive ground.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	785007998405
Country Of Origin	Mexico	Number of Receptacles	2
Features	Brass Mounting Strap	Outlet Type	Straight Blade
Application Sector	Commercial	Wall Plate Included	No

Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC		Warranty Type	1-Year Limited Warranty
Type	Outlet			
Dimensions				
Product Width US	1.322 in	Product Depth US	0.78 in	
Product Height US	2.635 in			
Listing Agencies / 3rd Party Agencies				
cULus ListingNumber	140596	cULus Listed	Yes	
Technical Information				
Operating Temperature Min	-40 °C	Dielectric Strength	Withstands 2000V minimum	
Connection Location	Back and Side	Number of Wires	3	
Operating Temperature Max	60 °C	Temperature Rating	-40° - 60° C	
Amperage	20 A	Number of Poles	Double Pole	
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor	
NEMA Configuration Code	6-20R	Operating Temperature	-40°-60°C	
Wire Connection Type	Screw Terminals	Voltage	250.0 V	