



Pass and Seymour  
20A 125V Hard Use Spec-Grade Duplex Receptacle, Back and Side Wire, Orange  
Part No. 5362OR



eHard Use Spec Grade Duplex Receptacle Back and Side-Wire 20A 125V Yellow

## Features & Benefits

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Two drive screws anchor strap to back body and face where abrupt removal torque is greatest.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.  
Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Orange
UPC Number	785007197761	Country Of Origin	United States
Number of Receptacles	2	Application Sector	Commercial
Standard	FEDSPEC	Warranty Type	1-Year Limited Warranty
Type	Outlet		

---

## Dimensions

---

Product Width US	1.32 in	Product Depth US	0.78 in
------------------	---------	------------------	---------

---

Product Height US	2.635 in
-------------------	----------

---

## Listing Agencies / 3rd Party Agencies

---

cULus Listed	Yes
--------------	-----

---

## Technical Information

---

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

---

Indoor/Outdoor	Indoor
----------------	--------

---