



Legrand

Hard Use Spec Grade Receptacle, Back & Side Wire, 20A, 125V, Red
Part No. 5362RED

eHard Use Spec Grade Duplex Receptacle Back & Side Wire 20amp 125volt Yellow



Features & Benefits

Corrosion-resistant, plated and tabbed steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

8 hole internal screw-pressure-plate back wire terminals accept #10 - #14 AWG solid or stranded copper or copper-clad conductors.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

Specifications

General Info

Color Red

UPC Number 785007536249

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Commercial

Standard UL498, CSA C22.2 No. 42

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140596

Technical Information

Number of Poles Double Pole

Voltage	125 V
----------------	-------

Connection	Back and side wire
-------------------	--------------------

Dielectric Strength	Withstands 2000V minimum
----------------------------	--------------------------

Temperature Rating	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
---------------------------	---

Wire Size	#14 - #10
------------------	-----------

Number of Wires	3
------------------------	---

Environmental Conditions	Flammability: UL94 V2
---------------------------------	-----------------------
