



Pass and Seymour
Hospital Grade Surge Protective Duplex Receptacle, Blue
Part No. 8200BLSP



Hospital Grade Surge Protective Duplex Receptacle offers increased transient protection, reliability and protection notification (Audible Alarm with LED Indicator). Back and Side Wire, 15amp 125volt, Ivory.

Features & Benefits

Solid-state LED monitor has 25-year minimum life expectancy. A high visibility, wide-angle lens indicates protection is in place.

LED Indication: Steady green = protected, Flashing red = not protected, OFF = no power to unit

Audible alarm alert of MOV damage. Alarm able to be turned On/Off.

Wrap-around steel strap for structural integrity. Auto-ground is standard, for easier installation.

Impact-resistant thermoplastic exterior resists impacts and scrapes.

Triple-wipe, copper-alloy contacts for superior, more dependable connection.

External screw-pressure-plate back and side wire terminals including ground with external back wire clamps (exclusive) accept #14 - #10 AWG copper or copper-clad, solid or stranded conductors.

External pressure plate feature allows two conductors to be terminated by a single screw.

Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.

Thermal protection in 3 modes. 3 17mm dual pack MOVs absorb up to 340 Joules of excess energy in each leg (L-N, L-G, N-G) with 24,000 amp current handling capability for full, equal and symmetrical protection.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Product Line	Pass & Seymour	Color	Blue
UPC Number	785007193527	Country Of Origin	Mexico

Application Sector	Commercial	Standard	cUL UL1449, UL498: CSA C22.2 No. 42: ANSI/IEEE C62.41 (Formerly IEEE 587), ANSI/IEEE C62.45 Installation Categories "A" (Ring Wave) "B" (Unidirectional Impulse).
--------------------	------------	----------	---

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Connection	Back and side wire	Class	IG
Amperage	15 A	Environmental Conditions	Flammability: UL94 V2