



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Brown
Part No. 5862

Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 250V



Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.	Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.
Strap tabs wrap around face to prevent strap from separating from face and back body.	Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
High strength nylon face.	Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.
Auto-ground clip assures positive ground.	For covering patents, see www.legrand.us/patents .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Brown
UPC Number	785007549003	Country Of Origin	Mexico
Number of Receptacles	2	Application Sector	Commercial
Standard	cULus UL498, CSA C22.2 No. 42, FEDSPEC	Type	Outlet

Dimensions

Product Width US	1.322 in	Product Depth US	0.78 in
------------------	----------	------------------	---------

Product Height US	2.635 in
-------------------	----------

Listing Agencies / 3rd Party Agencies

cULus ListingNumber	140596	cULus Listed	Yes
---------------------	--------	--------------	-----

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
---------------------	--------------------------	------------	--------------------

Number of Wires	3	Temperature Rating	-40° - 60° C
-----------------	---	--------------------	--------------

Amperage	20 A	Number of Poles	Double Pole
----------	------	-----------------	-------------

Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
-----------	-------------	----------------	--------

Environmental Conditions	Flammability: UL94 V2
--------------------------	-----------------------