



## Legrand

Heavy-Duty Spec Grade Receptacles, Back & Side Wire, 20A, 250V, Gray  
Part No. 5862GRY



Heavy-Duty Spec Grade Duplex Receptacle Back & Side Wire 20amp 250volt Black

### Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

.032 inch thick, brass, triple-wipe power contacts for lasting retention.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Eight back wire holes.

Auto-ground clip assures positive ground.

For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, [click here](#).

### Specifications

#### General Info

Color Gray

UPC Number 785007549027

Country Of Origin Mexico

Product Line Pass & Seymour

Application Sector Commercial

Standard cULus UL498, CSA C22.2 No. 42

#### Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140596

#### Technical Information

Number of Poles Double Pole

---

<b>Voltage</b>	250 V
----------------	-------

---

<b>Connection</b>	Back and side wire
-------------------	--------------------

---

<b>Dielectric Strength</b>	Withstands 2000V minimum
----------------------------	--------------------------

---

<b>Temperature Rating</b>	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact
---------------------------	---

---

<b>Wire Size</b>	#14 - #10
------------------	-----------

---

<b>Number of Wires</b>	3
------------------------	---

---

<b>Environmental Conditions</b>	Flammability: UL94 V2
---------------------------------	-----------------------

---