



Pass and Seymour
20A 250V Heavy Duty Spec-Grade Duplex Receptacle, Back and Side Wire, Gray
Part No. 5862GRY



Heavy-Duty Spec Grade Duplex Receptacle Back and Side Wire 20A 250V

Features & Benefits

Heavy-duty, brass strap for added strength and ground conductivity.

Strap tabs wrap around and lock down on face to prevent strap from separating from face and back body.

Strap tabs wrap around face to prevent strap from separating from face and back body.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

High strength nylon face.

Internal screw-pressure-plate back and side wired to accept #14 and #10 AWG stranded or solid copper or copper-clad conductors.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

| | | | |
|-----------------------|--|--------------------|------------|
| Product Line | Pass & Seymour | Color | Gray |
| UPC Number | 785007549027 | Country Of Origin | Mexico |
| Number of Receptacles | 2 | Application Sector | Commercial |
| Standard | cULus UL498, CSA C22.2 No. 42, FEDSPEC | Type | Outlet |

Dimensions

| | | | |
|------------------|----------|------------------|---------|
| Product Width US | 1.322 in | Product Depth US | 0.78 in |
|------------------|----------|------------------|---------|

| | |
|-------------------|----------|
| Product Height US | 2.635 in |
|-------------------|----------|

Listing Agencies / 3rd Party Agencies

| | | | |
|---------------------|--------|--------------|-----|
| cULus ListingNumber | 140596 | cULus Listed | Yes |
|---------------------|--------|--------------|-----|

Technical Information

| | | | |
|--------------------------|--------------------------|--------------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
| Amperage | 20 A | Number of Poles | Double Pole |
| Wire Size | 14 - 10 AWG | Indoor/Outdoor | Indoor |
| Environmental Conditions | Flammability: UL94 V2 | | |