



Heavy-Duty Spec Grade Single Receptacle Back and Side Wire 20A 250V



Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

One-piece heat-treated triple-wipe brass power contacts.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Impact-resistant nylon face and thermoplastic back body.

Internal screw-pressure-plate back wire capable of accepting #14 - #10 AWG solid or stranded copper or copper-clad wire.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For covering patents, see www.legrand.us/patents.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
UPC Number	785007549102	Country Of Origin	Mexico
Number of Receptacles	1	Application Sector	Commercial
Standard	UL498, CSA C22.2 No. 42, FEDSPEC	Type	Outlet

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
------------------	---------	------------------	----------

Product Height US	1.68 in
-------------------	---------

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	140596	cULus Listed	Yes
cUL Listed	Yes		

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		