



Pass and Seymour  
20A 125V Heavy Duty Hospital-Grade Single Receptacle, Back and Side Wire, Ivory  
Part No. 8301I



Heavy-Duty Hospital Grade Single Receptacle Back and Side Wire 20A 125V

## Features & Benefits

- Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.
- Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.
- Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.
- Auto-ground clip assures positive ground.
- For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click here.
- .032 inch thick, brass, triple-wipe power contacts for lasting retention.
- Impact-resistant nylon face and thermoplastic back body.
- Terminal compartments isolated from each other for positive conductor containment.
- For covering patents, see [www.legrand.us/patents](http://www.legrand.us/patents).
- Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.
- Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	Ivory
UPC Number	785007830378	Country Of Origin	Mexico
Number of Receptacles	1	Application Sector	Commercial, Hospital Grade
Standard	UL498, cUL/CSA C22.2 No. 42, FEDSPEC	Type	Outlet

### Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	3.68 in		
Listing Agencies / 3rd Party Agencies			
cUL ListingNumber	140596	cUL Listed	Yes
Technical Information			
Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Temperature Rating	-40° - 60° C
Amperage	20 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Environmental Conditions	Flammability: UL94 V2		