



Legrand

20A, 120/125V Combination Single-Pole Switch & Tamper-Resistant Single Receptacle, Ivory
Part No. 671TRI



Our standard Pass & Seymour combination switches allow you to add lights to any room in your home without having to add or replace wall boxes. This tamper-resistant version features a dual mechanical shutter system to help prevent the insertion of foreign objects, making it much safer and more convenient than plastic outlet caps. For detailed Tamper-Resistant receptacle information, visit our Tamper-Resistant Receptacles page.

Features & Benefits

Easily accessible break-off separate or common feed.

Two devices fit into the space of one.

Tamper-resistant version features dual mechanical shutter system to help prevent insertion of foreign objects.

Side wire #12 and #14 AWG.

Grounding combination devices meet NEC Requirements.

For covering patents, see www.legrand.us/patents.

Specifications

General Info

Color Ivory

UPC Number 785007240795

Countries Of Origin Mexico

Product Line Pass & Seymour

Application Sector Residential/Commercial

Type Combination

Standard UL20, UL498

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

cULus ListingNumber 140597

Technical Information

Number of Poles Single Pole

Voltage 120 V

Actuator Toggle

| | |
|------------------------------|-----|
| Contact Configuration | N-0 |
|------------------------------|-----|

| | |
|-------------------|-----------|
| Connection | Side wire |
|-------------------|-----------|

| | |
|-----------------------|---------------------|
| Contact Rating | 20 Amp, 120/125 VAC |
|-----------------------|---------------------|

| | |
|---------------|-----------------|
| Action | SP & Receptacle |
|---------------|-----------------|

| | |
|---------------------------------|-----------------------|
| Environmental Conditions | Flammability: UL94 V2 |
|---------------------------------|-----------------------|

| | |
|-------------------------|-------|
| Operating Cycles | 30000 |
|-------------------------|-------|
