



Heavy-Duty Hospital Grade Single Receptacle Back and Side-Wire 20A 250V

Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

Product Line	Pass & Seymour	Color	Light Almond
Finish	Matte	UPC Number	785007091021
Country Of Origin	Mexico	Number of Receptacles	1
Application Sector	Commercial, Residential	Standard	FEDSPEC
Type	Single		

Dimensions

Product Width US	1.32 in	Product Depth US	1.093 in
Product Height US	3.68 in		

Listing Agencies / 3rd Party Agencies

cUL ListingNumber	E140596	cUL Listed	Yes
-------------------	---------	------------	-----

Technical Information

Phase	Single	Number of Wires	3
Temperature Rating	-40° - 60° C	Amperage	20 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor		