



adorne Collection
adorne® sofTap™ Wi-Fi Ready Master Tru-Universal Dimmer, Magnesium
Part No. ADTP700RMTUM1



The sofTap Wi-Fi Ready Master Tru-Universal Dimmer works with virtually any 120V dimmable bulb or fixture, and pairs with the adorne Hub to create a smart Wi-Fi Lighting Control System for your home. Manually turn lights on/off or adjust their brightness with the soft tap of a finger, or enjoy mobile control and create custom lighting scenes to control lights through the Legrand Lighting Control app for smartphones or tablets. For 3-way, or multi-way applications, use one master device with additional remote devices. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less, fitting into an existing electrical box and wiring directly to the light.

Works with virtually any 120V dimmable bulb or fixture.

Self-calibrates when you select your fixture's lighting type, automatically setting the appropriate minimum voltage to eliminate flicker and poor performance.

Pair with a sofTap Wi-Fi Ready Remote Dimmer for 3-way control. Simply follow the provided instructions after installing to pair with the Master Dimmer.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
UPC Number	804428067795	Country Of Origin	United States
Features	Smart Lighting, Indicator Lights	Switch Type	sofTap
Number of Switches	1	Works With	Amazon Alexa, Google Assistant, Radio Frequency
Application Sector	Residential	Standard	cULus, FCC, UL 1472

Listing Agencies / 3rd Party Agencies

cULus Listed Yes

Additional Information

RoHS Conformant Yes

Technical Information

Frequency Rating	900 M (RF) Hz	Number of Gangs	1
Amperage	5.5 A	Bulb Compatibility	Universal, LED, Incandescent, Halogen, Fluorescent, CFL, Xenon, HID
Number of Poles	Single Pole, 3-Way, Multi-Location	Wattage	700 W
Mounting Type	Box	Voltage	120 V
Connection Type	Internal Pressure Plates	Load	Incandescent, Halogen, MLV, Fluorescent, and ELV, CFL, and LED bulbs
Environmental Conditions	0 to 80 (relative humidity, non-condensing)		
