

Heavy-Duty Hospital Grade Single Receptacle, Back and Side-Wire, 15A 125V



Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.

Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.

Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.

Tri-drive terminal and mounting screws.

For covering patents, see www.legrand.us/patents.

Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current.

Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

One-piece brass, triple-wipe power contacts for lasting retention.

Impact-resistant nylon face and thermoplastic back body.

Terminal compartments isolated from each other for positive conductor containment.

Auto-ground clip assures positive ground.

For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click [here](#).

Specifications

General Info

| | | | |
|-------------------|-----------------------------|--------------------|------------|
| Product Line | Pass & Seymour | Color | Ivory |
| Country Of Origin | Mexico | Application Sector | Commercial |
| Standard | UL498, cUL/CSA C22.2 No. 42 | | |

Dimensions

| | | | |
|------------------|---------|------------------|----------|
| Product Width US | 1.32 in | Product Depth US | 1.093 in |
|------------------|---------|------------------|----------|

| | |
|-------------------|---------|
| Product Height US | 3.68 in |
|-------------------|---------|

Listing Agencies / 3rd Party Agencies

| | | | |
|-------------------|--------|------------|-----|
| cUL ListingNumber | 140596 | cUL Listed | Yes |
|-------------------|--------|------------|-----|

Technical Information

| | | | |
|---------------------|--------------------------|------------|--------------------|
| Dielectric Strength | Withstands 2000V minimum | Connection | Back and side wire |
|---------------------|--------------------------|------------|--------------------|

| | | | |
|-----------------|---|--------------------|--------------|
| Number of Wires | 3 | Temperature Rating | -40° - 60° C |
|-----------------|---|--------------------|--------------|

| | | | |
|----------|------|-----------------|-------------|
| Amperage | 15 A | Number of Poles | Double Pole |
|----------|------|-----------------|-------------|

| | | | |
|-----------|-------------|---------|---------|
| Wire Size | 14 - 10 AWG | Voltage | 125.0 V |
|-----------|-------------|---------|---------|

| | |
|--------------------------|-----------------------|
| Environmental Conditions | Flammability: UL94 V2 |
|--------------------------|-----------------------|
