



radiant Collection
Discontinued - radiant® 20A Tamper-Resistant Branch Circuit AFCI Outlet, Black
Part No. AF202TRBK



AFCI outlets from the radiant® Collection detect and cut power during arc-fault occurrences, reducing the risk of electrical fires. Meeting National Electrical Code as an alternative to AFCI breakers, these outlets make it easier to recognize and fix trips right where they happen. Maximize safety, in style, with AFCI protection featuring the sleek, clean lines of radiant. 20A outlets are ideal for use with larger appliances, as well as to meet regional requirements (Chicago, Canada). Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Protects against fire caused by arc-fault occurrences. Unlike breaker alternatives, AFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

For more information on AFCI, visit:
www.afcisafetyreceptacles.org

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Extends protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Black
Country Of Origin	China	Number of Receptacles	2
Outlet Type	AFCI, Indoor, Residential, Tamper-Resistant		

Listing Agencies / 3rd Party Agencies

CSA Listed	Yes
------------	-----

Technical Information

Number of Gangs 1

Amperage

20 A

Mounting Type Box

Voltage

125.0 V
