



Pass and Seymour  
15A 125V Hospital-Grade Short Strap Single Receptacle, Back and Side Wire, White  
Part No. 8284W



Hospital Grade Short Strap Single Receptacle Back and Side Wire 15A 125V.

## Features & Benefits

Corrosion-resistant, plated steel strap locked in to face and back body to resist pulling away from face/body assembly.	One-piece brass, triple-wipe power contacts for lasting retention.
Easily accessed break-off, line-contact connecting tab for fast, easy split-circuit wiring.	Impact-resistant nylon face and thermoplastic back body.
Internal screw-pressure-plate back wire capable of accepting #14 : #10 AWG solid or stranded copper or copper-clad wire.	Terminal compartments isolated from each other for positive conductor containment.
Auto-ground clip assures positive ground.	For covering patents, see <a href="http://www.legrand.us/patents">www.legrand.us/patents</a> .
For compatible wall plate options, from our TradeMaster unbreakable plates to our radiant screwless plates to our metal wall plates, click <a href="#">here</a> .	Temperature Rise: Maximum 30°C temperature rise at full-rated current after 50 cycles of overload at 150% of rated current with direct current. Operating Temperature: Maximum continuous +60°C, minimum -40°C without impact

## Specifications

### General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007378610	Country Of Origin	Mexico
Number of Receptacles	1	Application Sector	Commercial, Hospital Grade
Standard	UL498, cUL/CSA C22.2 No. 42, FEDSPEC	Type	Outlet

### Dimensions

Product Width US	1.32 in	Product Depth US	1.018 in
Product Height US	1.68 in		

### Listing Agencies / 3rd Party Agencies

cUL ListingNumber	E140596	cUL Listed	Yes
-------------------	---------	------------	-----

---

Technical Information

Dielectric Strength	Withstands 2000V minimum	Connection	Back and side wire
Number of Wires	3	Amperage	15 A
Number of Poles	Double Pole	Wire Size	14 - 10 AWG
Indoor/Outdoor	Indoor	Environmental Conditions	Flammability: UL94 V2

---