



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. *GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect

Replaces any standard outlet with ease, in as little as 10 minutes

More color options available to fit any style, including finishes to match current hardware and lighting trends

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets

Compatible with the 1-Gang-Plus (1+ Gang) adorne Wall Plates only. Cannot be used in multi-gang installations

Specifications

General Info

Product Line	Pass & Seymour	Color	White
UPC Number	785007052657	Country Of Origin	China
Number of Receptacles	2	Application Sector	Residential
Standard	CULUS	Warranty Type	Limited Lifetime Warranty

Technical Information

Interrupt Rating	0.025 A	Phase	Single
Frequency Rating	60 Hz	Trip Range	4 to 6 mA

Connection	Side & Back Wire	Number of Gangs	1
Number of Poles	Double Pole	Mounting Type	Box
Voltage	125 VAC	Connection Type	Internal Pressure Plates
