




adorne Collection  
adorne® 20A Tamper-Resistant Self-Test GFCI Outlet  
Part No. AGFTR2202W4



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code\* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. \*GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

## Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Offers the capacity of a standard 20A outlet, in a uniquely contemporary design.

Replaces any standard outlet with ease, in as little as 15 minutes.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

## Specifications

### General Info

Color	White	UPC Number	785007052640
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Number of Receptacles	2
Warranty Type	Limited Lifetime Warranty	Standard	CULUS

### Technical Information

Number of Poles	Double Pole	Number of Gangs	1
-----------------	-------------	-----------------	---

---

Voltage	125 VAC	Mounting Type	Box
Trip Range	4 to 6 mA	Connection	Side & Back Wire
Frequency Rating	60 Hz	Phase	Single
Connection Type	Internal Pressure Plates	Interrupt Rating	0.025 A

---