




Wiremold
Ratchet-Pro 881 Series Multiple Service Floor Box Cover Kit
Part No. 881RC4ATCBK



Ratchet-Pro™ multiservice activation kit for 881PVC Floor Box comes complete with two (2) 20A duplex receptacles, (receptacles can be wired as standard or Isolated Ground), flange and slide holder, 881ADP Adapter, and 881DIV Divider. Provided with Wiremold CM Series Open System unloaded adapters, Ortronics Series II and TracJack adapters. Modular jacks sold separately. CAUTION: Not for use on concrete pours less than 4 1/2" (114mm) deep. Not for use when concrete is the finished floor. Use only for tile, carpet, or wood covered floors.

Features & Benefits

Ratchet-Pro™ multiservice activation kit for 881PVC Floor Box comes complete with two (2) 20A duplex receptacles, (receptacles can be wired as standard or Isolated Ground), flange and slide holder, 881ADP Adapter, and 881DIV Divider. Provided with Wiremold CM Series Open System unloaded adapters, Ortronics Series II and TracJack adapters. Modular jacks sold separately. CAUTION: Not for use on concrete pours less than 4 1/2" (114mm) deep. Not for use when concrete is the finished floor. Use only for tile, carpet, or wood covered floors.

Specifications

General Info

| | | | |
|--------------|--|--------------------|------------|
| Product Line | Wiremold | Color | Black |
| UPC Number | 786564013044 | Country Of Origin | Mexico |
| Construction | Not Assembled | Application Sector | Commercial |
| Standard | cULus Listed Nonmetallic Outlet Boxes: File E110748 Guide QCMZ. | Type | Floor Box |

Dimensions

| | | | |
|-------------------|--------------|-------------------|---------|
| Product Width US | 8.25 in | Product Weight US | 2.93 lb |
| Product Volume US | 255.23 cu in | Product Depth US | 8.25 in |
| Product Height US | 3.75 in | | |

Listing Agencies / 3rd Party Agencies

cULus ListingNumber E110748

cULus Listed

Yes

Buy American Act Compliance

NAFTA Yes

Additional Information

RoHS Conformant Yes

Technical Information

Number of Outlets 4
