




radiant Collection
radiant® Tamper-Resistant Outlet, Brown
Part No. 885TRCC8



Take a step up from the standard. This tamper-resistant duplex outlet installs easily for the basic power every home needs, while elevating your space with the sleek, clean lines of radiant® for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Replaces any standard outlet with ease, in as little as 10 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisible shutters" for an invisible effect.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Features durable, high-impact resistant thermoplastic construction.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

| | | | |
|-------------------|-------------------------|-----------------------|------------------------|
| Product Line | Pass & Seymour | Color | Brown |
| Country Of Origin | Mexico | Number of Receptacles | 2 |
| Outlet Type | Tamper-Resistant | Application Sector | Residential/Commercial |
| Warranty Type | 1-Year Limited Warranty | | |

Dimensions

| | | | |
|-------------------|---------|------------------|--------|
| Product Width US | 1.29 in | Product Depth US | 1.0 in |
| Product Height US | 4.2 in | | |

Listing Agencies / 3rd Party Agencies

| | |
|--------------|-----|
| cULus Listed | Yes |
|--------------|-----|

Technical Information

| | | | |
|---------------------|-----|----------|------|
| Is Tamper-Resistant | Yes | Amperage | 15 A |
|---------------------|-----|----------|------|

| | | | |
|-----------------|-------------|----------------|--------|
| Number of Poles | Double Pole | Indoor/Outdoor | Indoor |
|-----------------|-------------|----------------|--------|

| | |
|---------|---------|
| Voltage | 125.0 V |
|---------|---------|
