




adorne Collection
adorne® 15A 1-Gang Pop-Out Outlet, White
Part No. ARPTR151GW2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Provides additional power with 3-plug access when extended from wall.

Installs easily in as little as 15 minutes.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety.

Disappears back into the wall with a simple push when not needed.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	UPC Number	786776178609
Country Of Origin	China	Number of Receptacles	3
Features	Pop-Out	Device Front Face Size	Full-Size
Device Backbody Size	Plus-Size	Outlet Type	Pop-Out, Tamper-Resistant
Application Sector	Residential	Standard	CULUS
Warranty Type	Limited Lifetime Warranty	Type	Outlet

Dimensions

Product Width US	2.99 in	Product Depth US	2.6 in
Product Height US	4.88 in		

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Technical Information

Phase	Single	Connection	Side and Back Wire
Number of Wires	3	Number of Gangs	1
Amperage	15 A	Number of Poles	Double Pole
Wire Size	14 - 10 AWG	Indoor/Outdoor	Indoor
Mounting Type	Box	Connection Type	Internal Pressure Plates
Environmental Conditions	95% (relative humidity, non-condensing)		
