




adorne Collection
adorne® 15A Two-Gang Pop-Out™ Outlet
Part No. ARPTR152GM2



The cleverest way to add power and style, the Pop-Out Outlet extends to offer 3-plug access, then uniquely disappears back into the wall with a simple push when not in use. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Perfect anywhere you'd like to hide outlets when not in use, for added style and safety. Provides additional power with 3-plug access when extended from wall.

Disappears back into the wall with a simple push when not needed.

Installs easily in as little as 15 minutes.

Comes with a special frame for mounting and requires a deep electrical outlet (22.5 cubic inches). No new wires required for typical installation.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Color	Magnesium	UPC Number	786776178630
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Number of Receptacles	3
Warranty Type	Limited Lifetime Warranty	Standard	CULUS

Dimensions

Product Width US	4.8 in	Product Length US	4.7 in
Product Depth US	2.6 in		

Technical Information

Number of Poles	Double Pole	Number of Gangs	1
Voltage	125 VAC	Mounting Type	Box
Connection	Side and Back Wire	Phase	Single
Wire Size	#14 - #10 AWG	Number of Wires	3

Connection Type

Internal Pressure Plates
