



Ortronics

Avaya®/Nortel® AA1419048-E6 Compatible 1000Base-SX MMF SFP (mini-GBIC) Transceiver Module

Part No. AA1419048-E6-LEG

This Avaya/Nortel AA1419048-E6 compatible SFP transceiver provides 1000Base-SX throughput up to 550m over multi-mode fiber (MMF) at a wavelength of 850nm using a LC connector. Digital optical monitoring (DOM) support is also present to allow access to real-time operating parameters. Our transceiver is guaranteed to be 100% compatible with the equivalent Avaya/Nortel transceiver. This easy to install, hot swappable transceiver has been programmed, uniquely serialized and data-traffic and application tested to ensure that it will initialize and perform identically. It is built to meet or exceed the specifications of Avaya/Nortel, as well as to comply with multi-source agreement (MSA) standards to ensure seamless network integration.

Please Note: Installing Legrand transceivers does not void your network equipment warranty. Network equipment manufacturers all have guidelines stating that warranty support on their products will not be affected by installing a Legrand or any third party transceiver.

Features & Benefits

Transceiver type SX allows for connections up to 550m

850nm wavelength signaling

Supports Digital Optical Monitoring (DOM)

High speed 1-Gigabit connectivity

LC ports designed for use with Multimode fiber

Specifications

General Info

Product Line

Legrand

Color

Silver

UPC Number

757120668572

Country Of Origin

United States

Application Sector

Commercial/Industrial

Additional Information

RoHS Conformant

Yes

Product Has Potential to Contribute to LEED

Yes