



radiant Collection
Discontinued - radiant® Dead Front 20A Branch Circuit AFCI Outlet, White
 Part No. AF202DFW



Designed for applications where arc-fault protection is required but outlet access is not needed, and can be used to extend protection "downstream" on the circuit. The device detects and cuts power during arc-fault occurrences, reducing the risk of electrical fires. With the included indicator light and accessible test and reset buttons, it makes trips easier to recognize and fix than with AFCI breaker alternatives. Part of the radiant® Collection, it also features sleek, clean lines for a sophisticated look. Made exclusively for use with screwless Wall Plates from the radiant® Collection, sold separately.

Features & Benefits

Protects against fire caused by arc-fault occurrences. Unlike breaker alternatives, AFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

For more information on AFCI, visit:
www.afcisafetyreceptacles.org

Replaces any standard receptacle with ease, in as little as 10 minutes.

More color options available to fit any style.

Equipped with proven SafeLock protection feature: if critical components are damaged and protection is lost, power to the outlet is disconnected.

Extends protection to "downstream" outlets when used with feed-thru wiring configuration. Note: Will cut power to face and downstream outlets if wired incorrectly.

Features durable, high-impact resistant thermoplastic construction.

Complete the look with a sleek, screwless radiant® Wall Plate, and coordinate with other designer switches and outlets available from the radiant® Collection.

Specifications

General Info

Product Line	Pass & Seymour	Replaced by Part Number	AF203DFW
Color	White	Country Of Origin	China
Number of Receptacles	0	Outlet Type	AFCI, Dead Front, Indoor, Residential
Application Sector	Residential/Commercial		

Listing Agencies / 3rd Party Agencies

CSA Listed Yes

Technical Information

Interrupt Rating 4 A Frequency Rating 60 Hz

Trip Range 5±1 mA Connection Back and Side Wire

Number of Gangs 1 Amperage 20 A

Number of Poles Double Pole Mounting Type Box

Voltage 125.0 V
