




adorne Collection
adorne® 15A Single Tamper-Resistant Outlet, Magnesium
Part No. ARTR151M10



Designed with the same commitment to style and safety as the entire adorne Collection, this device is ideal as a dedicated outlet for large or stationary appliances, or in small or narrow areas where a single plug is needed. The single outlet features "invisi-shutters" for discreet tamper-resistance that keeps children safe without compromising on style.

Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

For complete installation, device must be paired with an adorne® screwless Wall Plate (not included). Available in a range of contemporary colors and stunning finishes.

Replaces a standard outlet with ease in as little as 10 minutes.

Creates a designated outlet, ideal for use with appliances or products and devices with larger plugs.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Specifications

General Info

Product Line	Pass & Seymour	Color	Magnesium
Finish	Frosted	UPC Number	785007404340
Country Of Origin	China	Number of Receptacles	1
Device Front Face Size	Full-Size	Device Backbody Size	Full-Size
Outlet Type	Tamper-Resistant	Application Sector	Residential
Standard	RoHS, CSA, cULus, UL, Conforms to NEMA WD-1 and WD-6	Warranty Type	Limited Lifetime Warranty
Type	Single, Tamper-Resistant		

Dimensions

Product Length US 1.33 in

Listing Agencies / 3rd Party Agencies

CSA Listed Yes cULus Listed Yes

CSA File Number C22.2 No.42

Additional Information

RoHS Compliant Yes

Technical Information

Seismic Tested No Connection Wired

Amperage 15 A Current Rating 15 A

Indoor/Outdoor Indoor Wattage 1875 W

Mounting Type Box Connection Type Internal Pressure Plates

Environmental Conditions Flammability Rating: UL 94 V2
