



Hospital Grade AFCI/GFCI specially designed and tested for rigorous healthcare applications.

Features & Benefits

Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI Hospital Grade AFCI/GFCI specially designed and GFCI make it easy to distinguish between a trip caused by an arc fault and a ground fault	and tested for rigorous healthcare applications
Separate indicator lights on the Dual-Function AFCI/GFCI Receptacles for AFCI and GFCI make it easy to distinguish between a trip caused by an arc fault and a ground fault	Two back-wire holes per termination add a wiring flexibility, eliminate pigtail and save box space
High-impact-resistant, thermoplastic construction for superior strength and durability	Ground terminal back-wire for fast installation
Two indicator lights, one for GFCI and one for AFCI. Easy to distinguish between trip caused by arc fault and trip caused by ground fault. GFCI indicator light flashes if device fails the self-test, signaling that the AFCI/ GFCI receptacle should be replaced	Auto-ground clip assures a positive ground to metal box
Part of the radiant® collection of wiring devices and wall plates	FSUL Listed (Federal Specification WC596)
Feed-through protection	Patented SafeLock® Protection—if critical components are damaged and ground fault protection is lost, power to the receptacle is disconnected
Prevents line-load miswire—no power to the face or downstream receptacles if wired incorrectly	

Specifications

General Info

Product Line	Pass & Seymour	Color	White
Finish	Matte	Country Of Origin	China
Number of Receptacles	2	Outlet Type	AFCI, GFCI, Indoor, Residential, Tamper-Resistant
Type	AFCI, Duplex, GFCI, Tamper-Resistant		

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Is Tamper-Resistant	Yes	Number of Gangs	1
Amperage	20 A	Is Weather Resistant	No
Indoor/Outdoor	Indoor	Mounting Type	Box
Voltage	125 V		
