




adorne Collection
adorne® 15A Tamper-Resistant Self-Test GFCI Outlet
Part No. AGFTR2152W4



Add contemporary style, safely, to kitchens, bathrooms and more, with GFCI Outlets from the adorne Collection. Meeting Electrical Code* for ground fault protection in the home, GFCI outlets make it easier to fix trips right where they happen – no more confusion or running to the breaker box. The adorne GFCI Outlets also self-test automatically every three seconds to ensure reliable protection from shock due to ground fault occurrences. *GFCI protection is required by code in bathrooms, kitchens, garages, basements, outdoor areas, and for any other outlets found within six feet of a sink or water source. GFCI outlets should always be used when replacing existing GFCI outlets during renovation. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Protects against shock caused by ground-fault occurrences. Unlike breaker alternatives, GFCI outlets make it easier to fix trips with a convenient reset button on the outlet.

Conducts an industry-leading automatic self-test every 3 seconds. If the device ever fails, the indicator light flashes to signal it should be replaced.

Configuration easily supports two plugs and offers the capacity of a standard 15A outlet, in a uniquely contemporary design.

Protects children with a patented tamper-resistant shutter system that prevents improper insertion of foreign objects, complete with "invisi-shutters" for an invisible effect.

Replaces any standard outlet with ease, in as little as 10 minutes.

More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Color	White	UPC Number	785007052626
Country Of Origin	China	Product Line	Pass & Seymour
Application Sector	Residential	Number of Receptacles	2
Warranty Type	Limited Lifetime Warranty	Standard	CULUS

Technical Information

Number of Poles	Double Pole	Number of Gangs	1
-----------------	-------------	-----------------	---

Voltage	125 VAC	Mounting Type	Box
Trip Range	4 to 6 mA	Connection	Side & Back Wire
Frequency Rating	60 Hz	Phase	Single
Connection Type	Internal Pressure Plates	Interrupt Rating	0.025 A
