



adorene Collection
adorene® Whisper™ Wi-Fi Ready Remote Switch
Part No. ASWRRRM1



Working in conjunction with an adorne Hub and a Whisper Wi-Fi Ready Master Switch for 3-way control. Use the switch to turn lights on/off with a light, fluid motion. And, create custom lighting settings to control lights from your smartphone or tablet via the Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home. Made exclusively for use with screwless Wall Plates from the adorne® Collection, sold separately.

Features & Benefits

Installs in 25 minutes or less.

Allows 3-way application when paired with a Wi-Fi Ready Master Switch, letting you control a light or fixture from an additional location without running new wires. Pair with the Wi-Fi Ready Master Switch via the easy-to-follow instructions.

Compatible with iOS and Android devices for app-based control, simply download the free Legrand Lighting Control app. Also compatible with Amazon Alexa and Google Home, and even integrates into advanced home automation systems.

Part of the adorne Wi-Fi Lighting Control System, this device requires the adorne Hub to operate. More color options available to fit any style, including finishes to match current hardware and lighting trends.

Complete the look with a stunning, screwless adorne® Wall Plate, not included. Available in a range of contemporary colors and finishes. Coordinate with other designer switches & outlets.

Specifications

General Info

Color	Magnesium	UPC Number	804428431411
Country Of Origin	China	Product Line	Pass & Seymour
Number of Switches	1	Application Sector	Residential
Warranty Type	1-Year Limited Warranty	Standard	UL, FCC, cULus, RoHS

Listing Agencies / 3rd Party Agencies

cULus Listed	Yes
--------------	-----

Additional Information

RoHS Conformant	Yes
-----------------	-----

Technical Information

Number of Poles	Single Pole, 3-Way, Multi-Location	Number of Gangs	1
Voltage	120 V	Mounting Type	Box

Supply Voltage

120 V

Connection Type

Internal Pressure Plates

Environmental Conditions

0 to 80 (relative humidity, non-condensing)
