



Wiremold  
**GFCI PLUGMOLD 5FT ALUMINUM 9 OUTLETS AND SELF TEST GFCI MODULE**  
Part No. AL20GB506TRGFI6



Plugmold® Multioutlet Systems are available in a wide variety of lengths and fittings and in a variety of finishes to provide versatile solutions for many applications. Plugmold options include single or alternating circuits, standard or isolated ground receptacles, GFCI protection, tamper-resistant protection, USB charging, Snapicoil® harnesses of prewired receptacles, and cord-ended units. Plugmold® Multioutlet Systems are available in black or ivory ScuffCoat™ finish, painted white or gray enamel steel, stylish stainless steel, anodized aluminum and durable textured ivory nonmetallic. The painted steel product works with many types of decor and is paintable to integrate with most color schemes. Durable stainless steel and anodized aluminum Plugmold products are corrosion-resistant, making them ideal for labs.

Features & Benefits

Compact, low profile appearance. Enhanced aesthetics and ideal for installations within minimal spaces.

Specifications

General Info			
Product Line	Wiremold	Color	Silver
UPC Number	786776188004	Country Of Origin	United States
Product Series	AL2000 Series	Number of Receptacles	5
Outlet Type	GFCI, Tamper-Resistant	Application Sector	Commercial, Education, Entertainment, Healthcare, Hospitality, Retail
Standard	cULus Listed Base & Blank Cover: File e4376 Guide RJBT, Multi-Outlet Assemblies: File E15191 Guide PVGT, Fittings: File E41751 Guide RJPR, Base & Blank Cover: Meets Article 386 of NEC, Plugmold Strips: Meets Article 380 of NEC	Warranty Type	1-Year from Installation or 2-Years from Day of Sale
Type	Plugmold	Installed Devices	Single Receptacle
Dimensions			
Product Weight US	3.1 lb	Receptacle Spacing	6 in
Listing Agencies / 3rd Party Agencies			
cULus ListingNumber	E15191	cULus Listed	Yes

Additional Information

RoHS Compliant      Yes

Technical Information

Is Pre-Wired      Yes      Wiring Configuration      Single Circuit

Amperage      15 A      Indoor/Outdoor      Indoor

Wiring Method      Hard-Wired      NEMA Configuration Code      5-15R

Mounting Type      On Surface      Voltage      125.0 V

Environmental Conditions      Dry interior locations