

acclAIM has redefined fiber architecture, replacing cassette-based solutions with direct connections, which eliminates extra components, and cost. acclAIM delivers the lowest insertion loss available on the market, the most optical headroom, improved density, flexibility and system lifecycle. The acclAIM™ Alignment Independent Multifiber (AIM) fiber interconnect system is designed to mate multiples of 8-fiber trunk cable connectors directly to arrays of twin-fiber patch cord connectors by means of a “conversion adapter”



Features & Benefits

Minimize Loss – Maximize

Optical Headroom
 Lowest loss pre-term Solution,
 Minimize or eliminate need for
 splicing, Maximize optical
 headroom to overcome barriers
 to performance

Design Smarter – Longer Lifecycle

Simplicity of design combined with application-defined on-site polarity adjustment, fewer components, and near-lossless performance enables acclAIM to provide a multi-generational lifecycle with a single installation of a sustainable building asset for decades to come

Ultra-High Density Plus (UHD+)
 Make the most of each rack unit
 (RU) with UHD+ offering up to
 192 fibers per RU (33% more
 than High Density)

Simplify Connectivity

No gender considerations – no pins, just direct connections; Direct-Mating Breakout – acclAIM connectors mate directly to an array of 2-fiber MDC duplex patch cords; Application-Defined Polarity – polarity can be adapted to nearly any link configuration; preplanned, on-site, or on the fly with no options to determine when ordering or designing; Improved accessibility – with the increased density of each connector and a smaller footprint enabled by acclAIM, there is more room to work on each panel

Reduce Labor – Lower Cost
 40% faster install; 60% faster
 removal; Single link testing
 after mating; Faster moves adds
 & changes

Approaching Infinite Scalability

Based on the simplified design, unparalleled performance, and architecture flexibility, Infinium acclAIM has an almost limitless migration path

Go Live Faster

Easy to stock and short lead
 times for conversion adapters
 enable rapid or emergency
 deployment

Typical Total Channel Connection Loss
 MM .45 dB, SM .40 dB

Specifications

General Info

Product Line	Ortronics	Country Of Origin	United States
--------------	-----------	-------------------	---------------